

KEYWORDS INDEX

activation energy: 149, 155, 157, 361, 370, 373
acylation: 19
adsorption: 81, 85, 89, 96, 97, 127, 131, 132, 133, 141, 142, 143, 161, 162, 164, 165, 166, 169, 173, 174, 217, 219, 220, 221, 222, 227, 234, 235, 236, 237, 240, 241, 242, 245, 258, 260, 370, 383, 411
agarose: 43, 45, 46, 48, 49, 50, 51, 52
amperometric detection: 249, 251
andisols: 387, 399
armed concrete: 305, 321
aroylation: 19
ascorbic acid oxidation: 71
association constant: 179, 180, 181, 184
camphor ligands: 3
carbon monoxide: 81, 372
carbon pencil electrodes: 375, 376, 377, 380, 382
carbon steel: 149, 161, 162, 163, 165, 167, 205, 206, 207, 218, 219
catalyst: 4, 93, 94, 96, 97, 99, 100, 361, 362, 363, 364, 365, 367, 368, 369, 370
cementation: 103, 104, 105, 106, 107, 108, 109, 110, 112, 113, 116, 117, 119, 120, 121
chronoamperometric technique: 193
C. I. Direct Red 80: 279, 280, 283
complexes: 3, 7, 8, 9, 11, 19, 20, 21, 22, 25, 26, 27, 28, 29, 30, 31, 33, 34, 38, 39, 40, 51, 87, 127, 128, 129, 130, 132, 133, 135, 137, 140, 142, 143, 144, 145, 146, 150
concrete: 305, 320, 321, 334, 335, 343, 344
conductivity: 88, 89, 149, 150, 151, 153, 154, 155, 157, 179, 180, 182, 183, 185, 252, 295, 303, 304, 387
copper: 9, 43, 44, 45, 46, 47, 48, 50, 51, 52, 53, 57, 58, 81, 82, 83, 85, 89, 103, 104, 105, 106, 107, 108, 109, 110, 113, 116, 117, 119, 206, 284, 285, 345, 359, 360, 367
copper oxide: 81, 82, 85
corrosion: 81, 90, 104, 127, 128, 131, 133, 134, 141, 147, 149, 161, 162, 164, 166, 167, 168, 169, 170, 172, 173, 174, 175, 205, 206, 209, 210, 211, 212, 213, 214, 215, 216, 217, 218, 219, 220, 221, 222, 223, 224, 225, 227, 228, 231, 232, 234, 236, 238, 239, 240, 241, 243, 245, 247, 263, 265, 266, 274, 282, 295, 296, 298, 299, 303, 305, 320, 321, 335, 345, 359, 360
corrosion inhibition: 127, 133, 141, 173, 227
corrosion inhibitor: 127, 128, 149, 161, 162, 174, 225, 247
corrosion rate: 141, 167, 205, 215, 220, 227, 305, 321, 335, 345
C-steel: 161, 166, 167, 168, 169, 171, 172, 173, 223
cyanoimide complexes: 19
cyclic voltammetric curves: 345

derivative: 19, 20, 22, 35, 127, 129, 133, 135, 138, 250, 254, 258
diamond electrode: 279, 280, 282, 285, 290, 292
dibutylsebacate: 149
dimethyl sulphoxide: 103, 120
donor- π -bridge-acceptor system: 11
DPASV: 55, 56, 59, 64, 65, 66
durability: 321, 343
dyeing house effluent treatment: 279
EIS: 81, 82
electrical resistance: 399
electrocatalysis: 71, 93, 100
electrochemical degradation: 279, 280, 284, 286, 287, 288, 289, 290, 291
electrochemical noise: 305
electrochemical reduction: 193
electrochemistry: 11, 13, 27, 28, 79, 203, 263, 293, 295, 304, 359, 374, 384, 409
electrolysis current: 399
electrolyte solution: 46, 179, 180, 182, 190, 192, 251, 254, 256, 283
electron richness: 19
electronic properties: 3, 86, 297, 375
electronic spectra: 11, 16
electronic structure: 263, 296, 303
electrophilic attack: 19, 20
electropolymerization: 377, 411
electro-remediation: 387, 399
FIA: 249, 250, 251, 252, 253, 254, 256, 258, 260
fractals: 375
fuel cell: 93, 94, 95, 96, 97, 99, 100, 361, 362
generalized corrosion: 345
grounding and lightning systems: 345
guar gum: 161, 162, 163, 164, 165, 166, 167, 171, 173, 174
heavy metals: 376, 382, 387, 399
ionic association: 179, 180, 189
iridium microelectrodes: 43, 47
iron nitroprusside: 71
isoelectric point: 81, 82, 83, 85, 89
lead: 43, 44, 45, 46, 47, 48, 49, 50, 51, 52, 53, 376
limiting molar conductivity: 179, 184
lineal polarization resistance: 335
linear polarization resistance: 345
low temperature effect: 179
manganese: 55, 56, 57, 59, 61, 64, 65, 66
mechanistic study: 411
methanol: 93, 94, 95, 96, 97, 98, 99, 100, 103, 112, 113, 119, 120, 121, 122, 361, 362, 363, 367, 368, 370, 371, 372, 373
methanol oxidation: 93, 96, 361, 362, 363, 367, 368, 370, 371, 372, 373
mild steel: 127, 128, 131, 133, 134, 135, 136, 137, 138, 139, 140, 141, 144, 145, 146, 147, 227
modified electrode: 71, 365, 375, 378
molybdenum complexes: 19, 127, 128, 132, 133, 135, 137, 140, 142, 143, 144
monitoring: 53, 305

NTA: 43, 44, 45, 46, 47, 48, 49, 50, 51, 52, 53
passive film: 81, 82, 86, 169, 170, 263, 295, 296, 297, 298, 299, 300, 301, 302, 303
petroleum plant: 205, 206
pitting corrosion: 161, 162, 167, 169, 170, 172, 345
pitting potential: 161, 169, 171, 174
plasticizer: 149, 150, 151, 152, 153, 157
platinum: 12, 25, 27, 28, 29, 30, 36, 39, 93, 94, 95, 100, 163, 182, 361
PLM: 43, 44, 46, 51, 52
polarization curves: 133, 134, 135, 138, 165, 166, 167, 169, 172, 345
polarization resistance: 134, 166, 207, 216, 221, 227, 305, 345
poly(4-vinylpyridine): 227, 228
polyaniline: 361, 372, 375, 376, 377, 381, 382, 384
polyphenylacetylene: 411
polypyrrole electrode: 279, 280, 281, 282, 288
pyridazine: 11
Randles-Sevcik: 375, 378, 381
redox properties: 3
regulatory capacity: 387
rotating zinc cylinder: 103, 104
ruthenium: 361
semiconducting properties: 81, 300, 302
soil pollution: 387
solid polymer electrolyte: 149
sour gases: 205, 208, 209, 215
stainless steel: 263, 282, 284, 295, 296, 298, 299, 300, 301, 302, 303
stress corrosion cracking: 295, 296, 298, 299, 303
sulfuric acid: 161, 227
SWSV: 43, 55, 56, 59, 63, 64, 65, 66
tin electrode: 193
topography: 375, 376, 378, 381, 383, 384
tubular electrodes: 55, 56, 57, 58, 249
uric acid: 249, 250, 252, 253
voltammetric cell: 55, 64, 66
voltammetry: 3, 4, 6, 7, 8, 11, 19, 20, 25, 27, 29, 39, 43, 45, 46, 53, 55, 56, 59, 63, 71,
81, 82, 93, 95, 96, 203, 363, 376
w/c ratio: 335